

## electronic pocket vernier calipers

angled internal/external measuring surfaces, knife-edge callipers

Mitutoyo

### Application:

For carrying out internal measurements, measuring wall thickness in holes, carrying out measurements within a groove

### Execution:

- Digimatic
- IP67
- AUTO OFF
- ABSOLUTE system for reliable measurement
- High-contrast display

### Advantage:

- Suitable for special or difficult to reach measuring points

### Delivery:

Delivered in box



<b>Art. no.</b>	<b>32018 097</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	573-742-20
<b>Min./max. length measuring range in inches</b>	0.4-8 in
<b>Data transmission type</b>	DIGIMATIC
<b>Depth gauge rod</b>	Without
<b>IP protection class</b>	IP 67
<b>With drive wheel</b>	Yes
<b>Error limit</b>	0.002 in
<b>Length of jaw</b>	70 mm
<b>Design</b>	Metric, Imperial
<b>Digit height</b>	9 mm
<b>Digit increment</b>	0.01 mm
<b>Digit increment in inches</b>	0.0005 in
<b>Type of locating</b>	With locking screw
<b>With mm / inch switching</b>	Yes
<b>Length</b>	290 mm
<b>With automatic shut off</b>	Yes
<b>Battery designation</b>	1,5 V SR44
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Weight of rechargeable battery/battery</b>	0.002 kg
<b>Battery voltage</b>	1.55 V
<b>Type of rechargeable battery/battery</b>	Silver oxide
<b>Calibration Group</b>	A
<b>ISO</b>	13385-1
<b>Functions</b>	Absolute function, ABS function, Origin (Dimension preset), Automatic switch-off, On/Off, With mm / inch switching
<b>Gross Weight</b>	0.590 kg
<b>Product Group</b>	3MA

### EAN

4946368726922