

Hammer drill GSB 2 1-2 RCT Professional

1300 watt

BOSCH

Application:

for the most demanding applications with large diameters (drilling, working with hollow drilling bits and hole saws) as well as screw-driving and mixing.

Advantage:

- clutch claws unlock and torque is minimised to prevent the tool blocking abruptly

Delivery:

Quick-action drill chuck, extra handle, depth stop, in plastic case



Art. no.	70021 048
Brand	BOSCH
Manufacturer Part Number	060119C700
Model	GSB 2 1-2 RCT
Manufacturer Article Number	060119C700
Nominal voltage	230 V
Max. drilling diameter in steel	16 mm
Max. drilling diameter in wood	40 mm
Max. drilling diameter in concrete	22 mm
Max. drilling diameter in masonry	24 mm
Power input	1300 W
Power output	695 W
Max. impact rate	51000 rpm
Idle speed 1st gear min./max.	0-900 rpm
Idle speed 2nd gear min./max.	0-3000 rpm
Min./max. drill chuck span width	1.5-13 mm
Drill chuck type	Quick action chuck
Weight	2.9 kg
With rubber-coated handle	Yes
With right/left-hand rotation	Yes
With electronic feedback	Yes
Gross Weight	5.210 kg
Product Group	731

EAN

3165140505642