


Typ Type Type	Bestell-Nr. Order No. No. de Cde	Nenn-Ø Nominal-Ø Ø nominal	Anschlussvariante Type of termination Type de raccordement	Metallteile / Oberfläche Metal parts / plating Partie métallique / traitement	Auszugskraft Withdrawal force Effort de débrochage	Obere Grenztemperatur Max. Temperature Température max.	Bemessungsstrom ¹⁾ Rated current ¹⁾ Intensité assignée ¹⁾	Kontaktwiderstand Contact resistance Résistance de contact
		mm			N	°C	A	mΩ



SA403	22.1053	4	M4	CuZn, Au	~5	150	50	0,3
--------------	----------------	---	----	----------	----	-----	----	-----



SA403N	22.1076	4	M4	CuZn, Ni	~5	150	50	0,8
---------------	----------------	---	----	----------	----	-----	----	-----



Montagematerial bitte separat bestellen, siehe Seite 15.

Assembly material, please order separately, see page 15.


Accessoires de montage à commander séparément, voir page 15.



SA404	22.1054	4	M3	CuZn, Au	~8	150	50	0,3
--------------	----------------	---	----	----------	----	-----	----	-----




SA404N	22.6012	4	M3	CuZn, Ni	~12	150	50	0,8
---------------	----------------	---	----	----------	-----	-----	----	-----



SA405	22.1055	4	M3	CuZn, Au	~5	150	50	0,3
--------------	----------------	---	----	----------	----	-----	----	-----



SA405N	22.6016	4	M3	CuZn, Ni	~5	150	50	0,8
---------------	----------------	---	----	----------	----	-----	----	-----



Montagematerial bitte separat bestellen, siehe Seite 15.

Assembly material, please order separately, see page 15.

Accessoires de montage à commander séparément, voir page 15.

¹⁾ je nach Anschlussart und Querschnitt

¹⁾ According to connecting method and cross section

¹⁾ Selon la méthode de raccordement et la section du conducteur