




PRODUCT SPECIFICATION

Brand	C.K
Product Range	Self grip wrench
Catalogue number	3630, 3641 & 3638
Date	22/03/2010

Range Description Self grip wrenches		 <p style="text-align: right;">3630</p>  <p style="text-align: right;">3638</p>  <p style="text-align: right;">3641</p>		
<p>3630</p> <ul style="list-style-type: none"> • Drop forged and hardened chrome vanadium jaws for strength and durability • Concave jaws ideal for gripping round materials • Integral wire cutting blades • Fine opening adjustment. • Quick release lever • Epoxy coated for corrosion resistance • Display packed 				
<p>3638</p> <ul style="list-style-type: none"> • Hot drop forged chrome vanadium jaws for strength and durability • Combination straight and curved jaws ideal for gripping round, flat and square section • Quick release lever • Epoxy coated for corrosion resistance • Display packed 				
<p>3641</p> <ul style="list-style-type: none"> • Hot drop forged chrome vanadium jaws for strength and durability • Flat jaws ideal for gripping flat surfaces • Quick release lever • Epoxy coated for corrosion resistance • Display packed 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3630 10	Self Grip Wrench 250mm	5013969488302	82041200	5
T3638 07	Self grip wrench 180mm	5013969488906	82041200	1
T3638 10	Self grip wrench 250mm	5013969489002	82041200	5
T3641	Self Grip Wrench 250mm	5013969489101	82041200	5

Technical product information	3638 - 250mm Max jaw capacity for round bar = 50mm 3638 - 180mm Max jaw capacity for round bar = 25mm Max jaw capacity for flat bar = 25mm 3638 - 250mm Max jaw capacity for round bar = 35mm Max jaw capacity for flat bar = 32mm 3641 - 250mm Max jaw capacity across flats = 40mm
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through normal wear and tear or inappropriate use is not covered
Country of origin	Germany

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3630 10	65	26	230	566	118	27	300	585
T3638 07	55	15	200	364	118	16	300	380
T3638 10	65	23	240	570	118	23	300	587
T3641	65	26	225	531	118	27	300	550

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3630 10	240	35	350	2948		
T3638 07	-	-	-	-		
T3638 10	260	45	330	2958		
T3641	240	35	330	2773		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3630 10	2	Tie	17	Backing card	23	Bag		
T3638 07	2	Tie	17	Backing card	8	Bag		
T3638 10	2	Tie	17	Backing card	23	Bag		
T3641	2	Tie	17	Backing card	23	Bag		