



Connector Location A




Connector Location B



X
male

Y
male

Loading-Plan:



- Temperature range: -40°C ... +70°C

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
All rights reserved Department HCS - RO		Created by COSTEA	Inspected by STOCHECIC	Standardisation MUNTEANV	Date 2018-09-13	State Final Release	
HARTING Customised Solutions D-32339 Espelkamp		Title RJ Industrial PROFINET cable assembly				Doc-Key / ECM-Nr. 100081054/UGD/051/G 500000139970	
		Type TB	Number 0945771XXXX			Rev. G	Page 1/3

1	2	3	4	5	6	7	8	
A								A
B	81	09457711183	RJ45 Ethernet trailing cable, AWG22/7, 2x2x0.75, PUR, Cat. 5+, green	100				B
	80	09457711182		90				
	79	09457711181		80				
	78	09457711180		70				
	77	09457711179		60				
	76	09457711187		55				
	75	09457711178		50				
C	74	09457711177		40				C
	73	09457711176		30				
	72	09457711175		20				
	71	09457711186		18				
	70	09457711174		15				
	69	09457711188		14				
	68	09457711189		12				
D	67	09457711173		10				D
	66	09457711172		9				
	65	09457711171		8				
	64	09457711170		7				
	63	09457711169		6				
	62	09457711168		5				
	61	09457711167	4					
E	60	09457711166	3				E	
	59	09457711190	2.3					
	58	09457711165	2					
	57	09457711164	1.5					
	56	09457711163	1					
	55	09457711185	0.6					
	54	09457711162	0.5					
	53	09457711184	0.3					
F	Cont. no.	Part no.	Type of cable	Dim. a[m]				F
	1	2	3	4	5	6	7	

	All rights reserved	Created by COSTEA	Inspected by STOCHECIC	Standardisation MUNTEANV	Date 2018-09-13	State Final Release	
	Department HCS - RO	Title RJ Industrial PROFINET cable assembly				Doc-Key / ECM-Nr. 100081054/UGD/051/G 500000139970	
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 0945771XXXX			Rev. G	Page 3/3