



SPECIFICATION

Product Name	Super Cam Max
Item Code	SRCAMV6.5MAX
Camera Length	7.7 cm
Camera Width	2.96 cm
Camera Weight	50g
Fits Hole Size	40 mm and above

APPLICATION

- Speed up visual inspections
- Accurate inspection reports/quotations
- Easier fault finding
- Safe working in hard-to-reach places
- Time-saving cable installation

ABOUT

20M WIRELESS INSPECTION CAMERA - WITH ON-BOARD MEMORY

The smarter way to Inspect

• INSPECT • ROUTE • CAPTURE DATA • WORK SAFE

Connect the Super Cam Max to any smart device and capture data. Work safer and smarter by streaming high resolution video to your smart device in real time.

- Maximum operating distance
- Wireless Range 20m with WiFi hotspot, onboard when signal is out of reach
- Compact and light design
- Customisable app icon layout
- 6 Adjustable bright white LEDs
- 180-Degree angle adaptor
- Includes 1m Telescopic Stick
- Compatible with Super Rod products
- Wireless range up to 20m
- Always up viewing mode
- 60 min Fast charge
- Auto/manual focus
- Non-contact voltage detector
- IP67 Dustproof and waterproof
- Built-in WiFi hotspot
- Record video with sound
- Digital pinch zoom
- Instructions available on the App

For more information visit www.super-rod.co.uk/supercammax

Download our free Super Cam App - Scan the QR Code to get the App or search for Super Rod



Requires Android V6.0 or later

Requires IOS V11.2 or later

Apple, the App Store and the Apple Logo are trademarks of Apple Inc., registered in the U.S. and other countries. Google Play and the Google Play logo are trademarks of Google LLC

SRCAMV6.5MAX - Super Cam Max Wireless Inspection Camera Specifications

Wireless Range	20m with WiFi Hotspot on board memory when signal is out of reach
Memory Capacity	16GB, 10,000 pictures 30h video recording
Frequency	2.4GHz WIFI
Camera Resolution	720p (1280 x 720) for both live and recorded videos
Operating Time	approx 90 mins (LEDs full) to 105 mins (LEDs off)
Charging Time	60 min fast charge
Viewing Angle	33 Degrees (Horizontal)
Charge Port	USB Type C
Battery Capacity	650mAh
Battery Type	lithium polymer
Operating Temperature	0 degrees to 35 degrees Celsius
Storage Temperature	-20 degrees to 45 Degrees Celsius
Charge Voltage	5V DC
Non-Contact Voltage Detector Sensitivity	best sensitivity 150 voltage AC and above - CATIII 600V
Non-Contact Voltage Detector Sensor Range	50V-1000V AC (Approx)
Adjustable bright white LEDs	6 white - control functionality via the app (off, 25%, half, full)
IP67	dustproof and waterproof with back cap on
Built in right angle adaptor	180 degrees

CONTENTS

* Fully compatible with Super Rod products

- 1 x Super Cam Max Wireless Inspection Camera with on-board memory
- 1 x Padded Case
- 1 x Flexi Lead*
- 1 x Gooseneck*
- 1 x Tuff Hook*
- 2 x Adaptors*
- 1 x Male Gender Changer*
- 1 x Super Magnet*
- 1 x 1m Telescopic Stick*
- 1 x Super Cam Set-up Guide