

ENGLISH

19in. Wallmount Cabinet


Technical Featues


Material 1,2 mm steel Color RAL 7035 Maximum Static Load Up to 70 kg. Finish Electrostatic Powder Paint

Standard Configuration

- Steel frame
- Glass door with cylindrical lock
- Openable side panels from inside for security
- 1 Pair of heavy duty 19" mounting rails
- Flatpack option available
- RoHS compliant, UL and Gost-R Certificated







Height U	External Width [W] mm	External Depth [D] mm	External Height [H] mm	Internal Width [W] mm	Internal Depth [D] mm	Height	19" Rails Adjustable Depth Range [c]	Weight kg	RS stock no.
6	600	400	366	510	360	266	110-305	21.36	8020327
6	600	560	366	510	520	266	110-465	24.26	8020320
9	600	400	488	510	360	408	110-305	24.62	8020324
9	600	560	488	510	520	408	110-465	27.82	8020333
12	600	450	645	510	360	541	110-305	28.01	8020336
12	600	560	621	510	520	541	110-465	31.65	8020330

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.