

Best Sellers

Order code	Manufacturer code	Description
60-4666	RWH-SS-106D	6V RWH SERIES 12A SPDT RELAY
60-4668	RWH-SS-112D	12V RWH SERIES 12A SPDT RELAY
60-4670	RWH-SS-124D	24V RWH SERIES 12A SPDT RELAY

Best Sellers	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003




- Pcb relay
- Standard pin-out
- 12A switch
- C-UL & TÜV Approval




UL E141060
TUV R9854380




Contact rating	15A @ 120VAC/24VDC
Maximum Voltage	240VAC/110VDC
Minimum Switching Load	15mA @ 5VDC
Contact Material	AgSnO ₂
Pull-in Time	10ms max
Release Time	5ms max
Dielectric strength contact/contact	500VAC @ 50/60Hz for 1 min
Dielectric strength coil/contact	1000VAC @ 50/60Hz for 1 min
Temperature range °C	-30 to +55
Life Expectancy – Mechanical	10 ⁷ Operations at no load
Life Expectancy - Electrical	10 ⁵ Operations at rated load



RW H-D SPST 360mW (450mW 48VDC)			RW H-D SPDT 360mW (450mW 48VDC)		
Coil VDC	Coil Ω ±10%	Part Number	Coil VDC	Coil Ω ±10%	Part Number
3	25	RW H-SS-103DM	3	25	RW H-SS-103D
5	70	RW H-SS-105DM	5	70	RW H-SS-105D
6	100	RW H-SS-106DM	6	100	RW H-SS-106D
9	225	RW H-SS-109DM	9	225	RW H-SS-109D
12	400	RW H-SS-112DM	12	400	RW H-SS-112D
18	900	RW H-SS-118DM	18	900	RW H-SS-118D
24	1600	RW H-SS-124DM	24	1600	RW H-SS-124D
48	6400	RW H-SS-148DM	48	6400	RW H-SS-148D



BOTTOM VIEW



BOTTOM VIEW