

# ACS480-04-02A7-4



ACS480-04-02A7-4 Pcont.max:0,75kW, lcont.max:2,5A

## General Information

Global Commercial Alias	ACS480-04-02A7-4
Product ID	3AXD50000047765
ABB Type Designation	ACS480-04-02A7-4
EAN	6438177458937
Catalog Description	ACS480-04-02A7-4 Pcont.max:0,75kW, lcont.max:2,5A

## Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044084
EAN	6438177458937
Invoice Description	ACS480-04-02A7-4 Pcont.max:0,75kW, lcont.max:2,5A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	FIPSEEXPU US Drive Services SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU FIDRIEXPU

## Technical

Frequency (f)	50/60 Hz
Input Voltage ( $U_{in}$ )	380 ... 480 V
Number of Phases	3
Output Current, Normal Use	2.6 A
Output Power, Light-Overload Use	0.75 kW
Output Power, Normal Use	0.75 kW

## Additional Information

Product Main Type	ACS480-04-02A7-4
-------------------	------------------

Product Name

Frequency Converter

---

Categories

---

Drives → Low voltage AC drives → General purpose drives

