

Caramba Maintenance and Repair Sprays

Caramba 6612011 Super Multi-Use-Spray



Ordering details: e.g.: Product No. 14070181,
Caramba Super Multi-Use-Spray

Product No.	Contents in ml	Weight in g
140 701 81	500	527

Caramba Multi-Use-Oil can be used as a rust remover, contact agent, corrosion protection and metal care product.

- very good lubricating properties.
- high moisture displacement and good corrosion protection.
- excellent creeping properties.
- well suited as a rust remover.
- silicone and resin-free.
- temperature range: -40°C to +180°C.
- Danger (5) H222, H229.

Caramba 6071851 High Performance White Spray Grease



Ordering details: e.g.: Product No. 14070182,
Caramba High Performance White Spray Grease

Product No.	Contents in ml	Weight in g
140 701 82	500	431

Caramba High Performance White Spray Grease for lubrication and corrosion protection of all types of heavily stressed parts.

- corrosion-protective.
- for high loads (VKA-Value: 1,400 N).
- very good creep ability.
- extremely spin-off resistant and water resistant.
- optimum lubrication of hard-to-reach places.
- temperature range: -30°C to +150°C (emergency lubrication by PTFE up to +250°C).
- Danger (1, 2, 5) H222, H229, H315, H336, H411.

Caramba 64540001 High Performance Wire Rope and Gear Grease



Ordering details: e.g.: Product No. 14070183,
Caramba High Performance Wire Rope and Gear Grease

Product No.	Contents in ml	Weight in g
140 701 83	500	469

Caramba High Performance Wire Rope and Gear Grease is a neutral, anthracite-coloured and odourless lubricant for demanding tribological tasks wherever components are subjected to high pressures.

- for high loads (VKA-Value: 2,100 N).
- salt and splash water resistant.
- optimum adhesion.
- prevents surface welding.
- temperature range: -30°C to +120°C (emergency lubrication up to +450°C).
- Danger (1, 2, 5) H222, H229, H315, H336, H411.

Caramba 60628501 High Performance Chain Spray



Ordering details: e.g.: Product No. 14070184,
Caramba High Performance Chain Spray

Product No.	Contents in ml	Weight in g
140 701 84	500	451

Caramba Chain Spray is a fully synthetic, colourless chain grease that is optimally suited for chains with high rotation speeds.

- extreme lubricity. (VKA-Value: 1,900 N).
- protects against wear and corrosion.
- spin-resistant and splash water resistant.
- high creep capacity.
- suitable for O-, X- und Z-rings.
- temperature range: -40°C to +200°C.
- Danger (1, 2, 5) H222, H229, H315, H411.

Caramba 60268176 High Performance Copper Paste



Ordering details: e.g.: Product No. 14070185,
Caramba High Performance Copper Paste

Product No.	Contents in ml	Weight in g
140 701 85	200	309

Caramba Copper Paste provides highly effective protective and lubricating coatings on parts exposed to high temperatures.

- protects against corrosion, Fixed burning and seizure.
- against noise and vibrations.
- facilitates installation and removal.
- due to its metal content, it is also ideal can also be used as a heat-conducting paste.
- temperature range: -30°C to +1,100°C.
- Attention (1, 2) H229, H319, H410.

Caramba 6103051 High Performance Silicone Spray



Ordering details: e.g.: Product No. 14070186,
Caramba High Performance Silicone Spray

Product No.	Contents in ml	Weight in g
140 701 86	500	473

Caramba Silicone Spray is a multifunctional lubricant and care product for metal, plastic and rubber.

- lubricates and maintains.
- release for the food processing industry (category H2 - NSF Reg. No. 142272).
- colourless and low odour, no staining.
- high water resistance prevents unwanted icing.
- temperature range: -30°C to +200°C.
- Danger (1, 2, 5) H222, H229, H315, H336, H411.

Caramba 690019 Intensive Cold Spray



Ordering details: e.g.: Product No. 14070187,
Caramba Intensive Cold Spray

Product No.	Contents in ml	Weight in g
140 701 87	500	440

Caramba Cold Spray facilitates the pressing of metal components such as ball bearings, bushings, chain links, shafts, etc. into tight fits. Can also be used for troubleshooting in electronic areas.

- versatile use.
- fast cooling up to -40°C.
- risk of frostbite at body contact.
- residue-free evaporation.
- Danger (5) H222, H229.

Caramba 63308401 Intensive Stainless Steel Cleaner



Ordering details: e.g.: Product No. 14070188,
Caramba Intensive Stainless Steel Cleaner

Product No.	Contents in ml	Weight in g
140 701 88	500	473

Caramba Stainless Steel Cleaner Spray cleans and protects all metal surfaces.

- protects against dirt and tarnishing.
- release for the food processing industry (category A7 - NSF Reg. No. 139339).
- removes dirt, lime stains, flash rust, grease, oils and resins.
- effective on stainless steel, aluminium, copper and brass.
- optimum protection against tarnishing.
- Danger (1, 5) H222, H229, H304, H319, H336, H412.

H222 Extremely flammable aerosol.
H225 Highly flammable liquid and vapour.
H229 Pressurised container: May burst if heated.
H304 May be fatal if swallowed and enters airways.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.



Safety Data Sheets at www.maedler.de in the section Downloads