



Part No. **TA090**

Sprung hook probe 1000 V CAT III, red

These probes feature a shrouded 4 mm socket allowing connection to a measurement instrument using a 4 mm "banana" plug test lead. The sprung hook opens up to 10 mm to grip items such as components, IC legs, or small conductors.

TA090 Sprung hook probe specifications	
Length	121 mm
Height	23 mm
Hook limit	10 mm
IEC 1010 rating	1000 V CAT III 20 A
Color	Red

