

## **Product information**

## 73 05 160 T

## **KNIPEX X-Cut®**

**Compact Diagonal Cutter** 

**DIN ISO 5749** 



- Cuts finest strands as well as multi-core cables and piano wires
- Powerful, light and universal
- Pliers with tether attachment point for mounting a fall protection system
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Box-joint design: highest stability with low weight
- Doubly supported joint axis for heavy duty
- Large opening width for thicker cables
- Cuts precisely, even through fine copper wires
- Compact, low-weight construction
- Universally usable, in the assembly, maintenance and production
- 40% less force required compared with standard diagonal cutters of the same length
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened





General	
Article No.	73 05 160 T
EAN	4003773080077
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	180 g
Dimensions	160 x 55 x 23 mm
Standard	DIN ISO 5749
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	

Technical details	
Cutting capacities soft wire (diameter)	Ø 4.8 mm
Cutting capacities medium hard wire (diameter)	Ø 3.8 mm
Cutting capacities hard wire (diameter)	Ø 2.7 mm
Cutting capacities piano wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple- stranded	Ø 12.0 mm
Drop Protection System	yes

technical change and errors excepted

## **KNIPEX** Quality – Made in Germany









