

WSM 1C

WSM 1C - Rechargeable soldering station with micro soldering iron WMRP and safety rest
Product no.: T0053293399N



Benefits

- › Portable soldering station – solder in the field with lightweight soldering station independent of external power supplies, for professional use in remote locations
- › Up to one hour on one charge - Solder up to 1 hour with fully charged battery
- › 5 minutes charging for 15 minutes soldering – fully recharged battery in 20 minutes for up to 1 hour soldering time
- › Extremely fast heat-up time – be ready to solder within 5 seconds; Fastest heat-up and recovery time with sensors close to the soldering tip for excellent heat transfer. No downtime, continuing workflow, excellent results
- › Broad range of RT Micro soldering tips - versatile performance with Weller active RT Micro (RTM) soldering tips range for soldering of micro and standard components covering the widest range of soldering applications
- › ESD-safe – especially designed for soldering in electrostatic exposed areas, and everywhere an ESD-safe assembly is required
- › Intuitive Touch display - all soldering functionalities at hand with intuitive touch display
- › Maximum process security - soldering temperature locking function for maximum process security
- › High temperature accuracy - high temperature accuracy ($\pm 9^{\circ}\text{C}$ ($\pm 17^{\circ}\text{F}$)) and temperature stability ($\pm 5^{\circ}\text{C}$ ($\pm 9^{\circ}\text{F}$)) for highest precision soldering jobs



Technical Data

Dimensions L x W x H (mm)	137 x 110 x 55
Dimensions L x W x H (inches)	5,39 x 4,33 x 2,17 Inch
Weight (approx.) in kg	0.41
Voltage	100-240 V AC / 12 V DC
Power	50 W
Channels	1
Temperature range (depends on tool) °C	100 - 400
Temperature range (depends on tool) °F	210 - 750
Temperature accuracy °C	± 9
Temperature accuracy °F	± 17
Temperature stability °C	± 5
Temperature stability °F	± 9
Equipotential bonding socket	Via 3,5 mm pawl socket on side of device
Display	Touch-Sensor-Technology
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---