

Product data sheet

Item No. 92.051.8358.0

Female connector GST18i5F B2 R V BL01

Device connectors, snap-in panel mount, GST18i5, 5 pole, female, springclamp connection, 50V, 20 A, material thickness 0,5 - 1,5 mm, colour of coding: light blue



Item No.	92.051.8358.0
EAN	4015573718340
Order Unit	100 Piece(s)

Certificates / Approvals

Technical data

General

Rated current	20 A
Rated voltage	50 V
Pollution degree	2
Mechanical coding	Code 5
Rated impulse voltage	4 kV
Interlockable	Yes
Color of coding/ contact carrier	Light blue
Marking of poles	

Connection Data

Connection cross section solid	2.5 mm ²
Connection cross section stranded	1.5 mm ²
Terminations per pole	2

Model

Model	female
Number of poles	5
Connection type	Tension clamp connection
Connecting thread metric	No thread
Degree of protection (IP)	IP40

Built-in component	Snap-in/screw-in
--------------------	------------------

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

Dimensions

Length	38 mm
Width	55 mm
Height	18.5 mm