

## Gro-Lux T5

F28W T5 I 8 GroLux Retail  
0002823



### Product features

- High level of blue and red radiation helps promote healthy plant growth. Enhanced the natural colours of aquatic plants and fish in aquariums. For lighting of fresh water aquariums. Recommended also for use in greenhouses and indoor gardens.



## PRODUCT OVERVIEW

Product name	F28W T5 I 8 GroLux Retail
Technology	Fluorescent
Lamp shape	Linear
Type	T5
Cap/Base	G5
Fixture rating	Open
General application	Hospitality, Retail, Residential & Consumer
ETIM Class	EC002962
Luminous flux (lm)	750
Light colour	GroLux
Wattage (W)	28
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	15000
Product EAN number	5410288028231

## DATA TABLE

### General data

Product name	F28W T5 I 8 GroLux Retail
Technology	Fluorescent
Lamp shape	Linear
Type	T5
Cap/Base	G5
Fixture rating	Open
General application	Hospitality, Retail, Residential & Consumer
Operating temperature range (°C)	-15°C...+50°C
ETIM Class	EC002962

### Optical data

Luminous flux (lm)	750
Light colour	GroLux
Adjustable chromaticity	N

## Gro-Lux T5

*F28W T5 / 8 GroLux Retail*  
0002823

### Electrical data

Wattage (W)	28
Control gear required	Yes
Transformer required	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	370

### Lifetime data

Average life (Nominal) (h)	15000
----------------------------	-------

### Physical data

Max. Length base to base (mm) - A	589.8
Length base to pin Min-Max (mm) - B	594.5-596.9
Max. Lamp Diameter (mm) - D	17
Weight (kg)	0.054

### Packaging

Single packaging type	Carton
Product EAN number	5410288028231
Packaging single length / height (cm)	67.3
Packaging single width (cm)	2.7
Packaging single depth (cm)	2.7
DUN14 (outer)	15410288028238
Units per outer package	10
Packaging outer length / height (cm)	70.5
Packaging outer width (cm)	6.5
Packaging outer depth (cm)	14.6

### Safety data

Lamp mercury content (mg)	6
Optimal operating condition (°C)	-15-50
Breakage cleaning instructions	Applicable
Special purpose lamp	Yes
Suitable for household illumination	No
Safety message	Not suitable for household

## TECHNICAL DRAWINGS

