

# Compressed air tubing, Series TU1-S-PUR

- suitable for dynamic laying
- Ø 8 mm
- Polyester polyurethane
- Max. working pressure at 20 °C 10 bar



Max. working pressure at 20 °C 10 bar  
 Ambient temperature min./max. -30 ... 80 °C  
 Weight 0,03 kg

## Technical data

Part No.	external	Wall thickness	Color	Length	Winch	Bending radius min.
	-Ø			Delivery unit		At 20 °C
1820712023	8 mm	1,15 mm	Red	25 m	-	30 mm
1820712080	8 mm	1,15 mm	Green	25 m	-	30 mm
R412014557	8 mm	1,15 mm	Natural	50 m	-	30 mm
R412009989	8 mm	1,15 mm	Black	50 m	-	30 mm
R412009990	8 mm	1,15 mm	Blue	50 m	-	30 mm
1820712008	8 mm	1,15 mm	Natural	100 m	-	30 mm
1820712016	8 mm	1,15 mm	Black	100 m	-	30 mm
1820712028	8 mm	1,15 mm	Red	100 m	-	30 mm
1820712038	8 mm	1,15 mm	Blue	100 m	-	30 mm
R412004862	8 mm	1,15 mm	Yellow	100 m	-	30 mm
R412007800	8 mm	1,15 mm	Blue	500 m	-	30 mm
R414009118	8 mm	1,15 mm	Blue	600 m	Winch	30 mm

price / m

## Technical information

External calibrated  
 Suitable for dynamic laying  
 Halogen-free


## Technical information

Material

Material	Polyester polyurethane
----------	------------------------

## Diagrams

### Pressure-Temperature-Diagram



D = pressure resistance

T = temperature