


# Piggyback Terminal



## FEATURES:

Vinyl insulated  
Double crimp  
PVC  
Funnel entry



## SPECIFICATION:

Cross-section	4...6 mm <sup>2</sup>
Colour	Yellow
Diameter	6.5 mm
Material	Brass
Insulation material	Vinyl
Surface material	Tin-plated
Thickness	0.4 mm
Temperature range	max. +105 °C
Length	26 mm
Width	6.7 mm
Contact	6.3 x 0.8 mm



UL certified: E502428

Art. Nr.

RND 465-00603