




## SHM-1260 SERIES



1. Rating: DC6V 0.3A
2. Circuit: 1P2T
3. Timing: Non-Shorting
4. Travel: 2mm
5. Operating Force: 200±100gf

| Model No. | Knob"L" |
|-----------|---------|
| SHM-1260  | 2.0mm   |


## SHM-1270 SERIES



1. Rating: DC6V 0.3A
2. Circuit: 1P2T
3. Timing: Non-Shorting
4. Travel: 2mm
5. Operating Force: 150±100gf

| Model No.  | Description                      |
|------------|----------------------------------|
| SHM-1270   | lock with embossing cover        |
| SHM-1270N  | lock without embossing cover     |
| SHM-1270R  | non lock with embossing cover    |
| SHM-1270RN | non lock without embossing cover |



## SHM-1290AN SHM-1290BN



1. Rating: DC4V 0.3A
2. Circuit: 1P2T
3. Timing: Non-Shorting
4. Travel: 1.5mm
5. Operating Force: 150±100gf

| Model No.  | Knob"T" |
|------------|---------|
| SHM-1290AN | 0.4mm   |
| SHM-1290BN | 1.1mm   |


## SHM-1290AP SHM-1290BP



1. Rating: DC4V 0.3A
2. Circuit: 1P2T
3. Timing: Non-Shorting
4. Travel: 1.5mm
5. Operating Force: 150±100gf

| Model No.  | Knob"T" |
|------------|---------|
| SHM-1290AP | 0.4mm   |
| SHM-1290BP | 1.1mm   |

## SHM-1300 SERIES



1. Rating: DC4V 0.3A
2. Circuit: 1P3T
3. Timing: Non-Shorting
4. Travel: 1.5mm + 1.5mm
5. Operating Force: A→B, C→B =150±100gf  
B→A, B→C =200±150gf

| Model No.  | Knob"T" | cover "G" |
|------------|---------|-----------|
| SHM-1300AN | 0.4mm   | NO        |
| SHM-1300BN | 1.1mm   | NO        |
| SHM-1300AP | 0.4mm   | YES       |
| SHM-1300BP | 1.1mm   | YES       |