

M23 FEMALE, 0° 19 POLE

PUR 12x0.34+3X0.75 GRAY, drag ch 5m

M23

Female straight

19-pole

15-pole used


for 6-way distribution boxes, 5-pole

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

15	white
7	gray/ pink
5	green
4	red/ blue
	yellow
16	white/ green
8	gray
3	brown/ green
14	pink
17	white/ yellow
9	red
2	yellow/ brown
13	brown 0.75 mm ²
19	blue 0.75 mm ²
6	green/ yellow 0.75 mm ²
12	

Female



Product may differ from Image

Form

23231

Technical Data

Operating voltage	125 V AC/DC
Operating current per contact	max. 7.5 A
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Locking of ports	Screw thread M23 × 1 mm

Cables

Cable number	388
No./diameter of wires	12×0.34 + 3×0.75 mm ²
Wire isolation	PVC (yebr, rd, grpk, wh, rdbl, gn, whgn, ye, brgn, gr, whye, pk, br, gnye, bl)
C-track properties	2 Mio.
Jacket Color	gray
Shore hardness outer jacket	80 ± 5A
Material (jacket)	PUR/PVC
Outer diameter	approx. 9.8 mm
Bend radius (fixed)	10 × outer Ø
Bend radius (moving)	12 × outer Ø
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1