

SIMATIC WINCC RUNTIME CLIENT FROM V6.0 TO V7.0 SP3,
FOR WINCC RT CLIENTS (RT128), INCL. DRIVER, USER
ARCHIVE, ARCHIVE, CONNECTIVITY PACK




Figure similar

General information

Multi-user system

• Multiuser capability	Yes
• Number of servers, max.	12
• Number of clients for server without operator console, max.	32
• Web clients	Yes

Operator control and monitoring

Object block library	Yes; Integrated
Alarm logging system (incl. buffer and acknowledgment)	Yes; Integrated
Report system/log system	Yes
SQL database	Yes; Integrated
Process diagnostics	No
Sector-specific and technological expansions	No

Recipes/user archives

• User archive/recipe management	No
----------------------------------	----

Interfaces

Programming interfaces	Yes
OPC-DA interface, Server	Yes
OPC-DA interface, Client	Yes

Hardware requirements

Processor clock frequency, min.	1 GHz
Main memory, min.	1 000 Mbyte

Operating systems

Executable for operating system

- Windows 7 Yes

Configuration

Number of multi-user configurations, max. 32

Online configuration Yes

Script languages (Runtime)

- Number of Visual Basic Scripts Yes
- other Yes

Know-how protection

- Password protection Yes

Languages

Configuration languages

- Number of configuration languages 70

last modified: 12.03.2015