




Orthomat® Ribbed

Ribbed anti-fatigue mat for dry workplaces



- Versatile single layer foam anti-fatigue mat.
- Insulates standing workers against the effects of cold concrete floors.
- Lightweight, so easy to transport and reposition.
- Best suited to dry environments.
- High visibility version available with bright yellow borders.
- Ideal for lighter industrial use.
- Stylish ribbed surface pattern.
- Available in mats and rolls.
- Fire tested to BS EN 13501-1.



Parts

| Part Number | Size | Colour | Weight |
|-------------|--------------------------|--------|----------|
| AL010001 | 0.6 m x 0.9 m | Black | 1.50 kg |
| AL010002 | 0.9 m x 1.5 m | Black | 3.00 kg |
| AL010003 | 0.9 m x 18.3 m | Black | 38.00 kg |
| AL010003C | 0.9 m x per linear metre | Black | 2.00 kg |
| AL010004 | 1.2 m x 18.3 m | Black | 51.00 kg |
| AL010004C | 1.2 m x per linear metre | Black | 4.00 kg |
| AL010006 | 0.6 m x 18.3 m | Black | 31.00 kg |
| AL010006C | 0.6 m x per linear metre | Black | 1.70 kg |
| AL060001 | 0.6 m x 0.9 m | Grey | 1.50 kg |
| AL060002 | 0.9 m x 1.5 m | Grey | 3.00 kg |
| AL060003 | 0.9 m x 18.3 m | Grey | 38.00 kg |
| AL060003C | 0.9 m Linear m | Grey | 2.00 kg |
| AL060004 | 0.6 m x 18.3 m | Grey | 25.00 kg |
| AL060004C | 0.6 m Linear m | Grey | 1.90 kg |
| AL060005 | 1.2 m x 18.3 m | Grey | 51.00 kg |

Technical Specification

| | |
|--|---|
| Material | Open Cell PVC (Foam) |
| Surface Finish | Ribbed |
| Product Height | 9.5 mm |
| Size of Safety Border | 100 mm |
| Operating Temperature | 0°C to +60°C |
| Environmental Resistance | Suitable for dry indoor environments |
| Typical Applications | Production lines, Assembly areas, Packing stations, Workbenches |
| Installation Method | Loose lay |
| Cleaning Method | Brush/mop the top surface |
| Fire Tested to | BS EN 13501-1 Class Dfl - s1 |
| Country of Origin | China |
| Guarantee | 1 year when used in a dry environment |
| Adhesive recommended by F.Ball for permanent bond | F44 |

Parts

| | | | |
|-----------|--------------------------|-------------|----------|
| AL060005C | 1.2 m Linear m | Grey | 4.00 kg |
| AL060006 | 0.6 m x 0.9 m (x3) | Grey | |
| AL060701 | 0.6 m x 0.9 m | Grey/Yellow | 1.50 kg |
| AL060702 | 0.9 m x 1.5 m | Grey/Yellow | 3.00 kg |
| AL060703 | 0.9 m x 18.3 m | Grey/Yellow | 38.00 kg |
| AL060703C | 0.9 m x lin. m | Grey/Yellow | 2.00 kg |
| AL060704 | 1.2 m x 18.3 m | Grey/Yellow | 51.00 kg |
| AL060704C | 1.2 m x per linear metre | Grey/Yellow | 4.00 kg |

Technical Specification

Tackifier recommended by F.Ball F41

Adhesive recommended by F.Ball for heavy-duty/wet areas F74, F81, F84

Get in touch | To order FREE samples or arrange a site visit please call +44 (0)116 240 1088 or email sales@cobaeurope.com