

19-inch network cabinet Pro

roline[®]
Designed for Professionals

Data sheet



The network cabinets in the ROLINE Pro series were developed to enable particularly convenient and flexible network cabling. Each cabinet consists of a robust steel construction with a material thickness of up to 1.5 mm sheet steel. It is possible to change the door hinge. The cabinets can also be completely dismantled if required.

Characteristics:

- Load capacity: 800 kg
- Front door made of lateral metal struts with safety glass
- Locking system with swivelling lever handle on front door; 1-point locking on all doors
- Side panels are lockable and removable
- Pre-assembled 4 levelling feet
- Base with slide-on cable inlet
- Roof with cut-out for fan modules and removable lid
- Incl. fastening material
- Colour: Light grey, RAL 7035 or Jet black, RAL 9005
- IP protection class: IP20
- Mounted: Yes

19-inch network cabinet Pro

roline[®]
Designed for Professionals

Data sheet

The ROLINE Pro series offers a versatile selection of network enclosures in various height units from 16 U to 47 U and in the

colours grey (RAL 7035) and black (RAL 9005).

Manuf. no.	Height	Width (mm)	Depth (mm)	Colour / RAL
26.21.0048	16 U	600	800	grey / RAL 7035
26.21.0217	16 U	600	800	black / RAL 9005
26.21.0049	22 U	600	600	grey / RAL 7035
26.21.0218	22 U	600	600	black / RAL 9005
26.21.0050	22 U	600	800	grey / RAL 7035
26.21.0219	22 U	600	800	black / RAL 9005
26.21.0051	22 U	800	800	grey / RAL 7035
26.21.0220	22 U	800	800	black / RAL 9005
26.21.0052	26 U	600	600	grey / RAL 7035
26.21.0221	26 U	600	600	black / RAL 9005
26.21.0053	26 U	600	800	grey / RAL 7035
26.21.0222	26 U	600	800	black / RAL 9005
26.21.0055	26 U	800	800	grey / RAL 7035
26.21.0224	26 U	800	800	black / RAL 9005
26.21.0054	26 U	800	1000	grey / RAL 7035
26.21.0223	26 U	800	1000	black / RAL 9005
26.21.0056	32 U	600	600	grey / RAL 7035
26.21.0225	32 U	600	600	black / RAL 9005
26.21.0057	32 U	600	800	grey / RAL 7035
26.21.0226	32 U	600	800	black / RAL 9005
26.21.0058	32 U	800	800	grey / RAL 7035
26.21.0227	32 U	800	800	black / RAL 9005
26.21.0060	36 U	600	800	grey / RAL 7035
26.21.0229	36 U	600	800	black / RAL 9005
26.21.0059	36 U	800	600	grey / RAL 7035
26.21.0228	36 U	800	600	black / RAL 9005
26.21.0062	42 U	600	600	grey / RAL 7035
26.21.0231	42 U	600	600	black / RAL 9005
26.21.0063	42 U	600	800	grey / RAL 7035
26.21.0232	42 U	600	800	black / RAL 9005
26.21.0061	42 U	600	1000	grey / RAL 7035
26.21.0230	42 U	600	1000	black / RAL 9005
26.21.0066	42 U	800	800	grey / RAL 7035
26.21.0235	42 U	800	800	black / RAL 9005
26.21.0064	42 U	800	1000	grey / RAL 7035
26.21.0233	42 U	800	1000	black / RAL 9005
26.21.0065	42 U	800	1200	grey / RAL 7035
26.21.0234	42 U	800	1200	black / RAL 9005
26.21.0068	47 U	600	600	grey / RAL 7035
26.21.0237	47 U	600	600	black / RAL 9005
26.21.0069	47 U	600	800	grey / RAL 7035
26.21.0238	47 U	600	800	black / RAL 9005
26.21.0067	47 U	600	1000	grey / RAL 7035
26.21.0236	47 U	600	1000	black / RAL 9005
26.21.0070	47 U	800	800	grey / RAL 7035
26.21.0239	47 U	800	800	black / RAL 9005

19-inch network cabinet Pro

roline[®]
Designed for Professionals

Data sheet



Tempered glass front door



Rear panel with cable feed



Removable side walls



Locking system with swivel lever handle



Base plate with cable feed



Roof with cut-outs for ventilation