



SFP+ Passive Copper Cables

Volex's SFP+ passive copper cable assemblies are a cost-effective, low-power alternative to optical modules for short reach links in high-speed interconnect applications such as high performance computing (HPC), enterprise network switching and network storage deployments. These assemblies support data transfer rates up to 10+ Gb/s per lane, meeting or exceeding current standards specifications.

Volex's SFP+ assemblies combine twin-axial shielded cable with robust die cast housing, integrated EMI shield, and actuating pull latch. The overmold technique used in fabrication for these cables provides additional strain relief and minimizes conductor pistoning. These assemblies can be integrated into belly-to-belly and side-stacked configurations

Features and Specifications

Product Type	Passive Copper
Conductor Sizes	25 – 30 AWG conductor sizes available to achieve maximum performance up to 7m
Conductor Treatment	Laser Stripped Conductors
Cable Type	PVC
Cable Color	Black
Packaging	PE Bag
Power Supply Voltage	3.3 V
Temperature Range	0 – 70° C
Retention Force	Minimum 90 N, Maximum 170 N
Insertion Force	Maximum 18 N
Options Include	Customer specified EEPROM Map Cable length Low Smoke, Zero Halogen (LSZH) jackets Custom colors for pull tab and cable jacket

Volex reserves the right to change specifications and availability without prior notice

APPLICATIONS

- Ethernet 10G
- Fiber Channel 8G
- FCoE 10G
- Networking
- Storage
- Hubs, switches, routers, servers, NIC's


STANDARDS COMPLIANCE

- Electrical: SFF-8419
- Mechanical: SFF-8432
- Memory Map: SFF-8472
- RoHS

Mechanical Drawing



END VIEW



VOLEX P/N	CABLE LENGTH, M	AWG	CABLE DIAMETER, MM
VSFPP30YP050	0.50	30	6.6
VSFPP30YP075	0.75	30	6.6
VSFPP30YP100	1.00	30	6.6
VSFPP30YP150	1.50	30	6.6
VSFPP30YP200	2.00	30	6.6
VSFPP30YP250	2.50	30	6.6
VSFPP28YP300	3.00	28	7.5
VSFPP28YP400	4.00	28	7.5
VSFPP26YP500	5.00	26	8.8

25–30 AWG conductor sizes are used to achieve maximum performance up to 7m.

Options available

- Low Smoke, Zero Halogen (LSZH) jackets
- Custom cable lengths up to 7m
- Custom colors for pull tab
- Custom EEPROM mapping

Contact us at sales@volex.com for assistance in finding the right solution for your needs.

VOLEX WORLDWIDE: MANUFACTURING ● SALES OFFICES ● DISTRIBUTION HUBS ●



Americas

Volex Inc.- Austin, TX
 Tel: +1 (800) 246 2673
 Email: sales@volex.com



Asia Pacific

Volex Inc.- Singapore
 Tel: +65 6788 7833
 Fax: +65 6788 7822
 Email: salesAP@volex.com



Greater China

Volex Interconnect Systems (Suzhou, China) Co., Ltd
 Tel: +86-512-6258-6673
 Fax: +86-512-6275-6670
 Email: salesGC@volex.com

EMEA

Volex Europe Ltd
 Co.Mayo, Ireland
 Tel: +353 9490 37480
 Email: sales@volex.com