


ART.: 810711333001

DLSB100 LED OPAL COVER - 95 mm



Art.: 810711333001, DLSB100 LED, Opal-white pmma diffuser, 14W, 3000K, Driver static, Direct, White, Recessed round LED downlight for indoors, consisting of: Multi-purpose die-cast aluminium housing combines all functions: heat-sinking, ceiling trim, ceiling brackets and gear tray connection, Light-tight housing, Suitable for ceiling tile thickness from 1-25 mm Recessed frosted diffuser for optimal light distribution and high homogeneity, White modular reflector, ABS injection-molded with light-tight connection of LED board, Excellent heat dissipation through die-cast aluminium heat sink with FAST (Flexible Air Stream) Technology, Colour rendering index Ra > 80, Colour tolerance according to MacAdam ≤ 3 SDCM Also dimmable via TouchDIM®, Complete with electric converter, Protection class IP20 (IP54 for light emission surface for installation in closed ceilings)

Connected load	14 W
Luminous flux	1060 lm
Efficiency	76 lm/W
Colour temperature	3000K
Colour rendering (CRI)	80
IP class	20
Nominal voltage	220 – 240 V
Colour	RAL 9016
UGR	25,6

