

RANA T5 600

RANA R 600 Bright Louvre 4x14W DALI MPM 840

0049710



Product features

- Ceiling recessed T5 luminaire, 592 x 594 x 46mm, Bright Aluminium Reflector 98% reflectivity, 4 x 14W T5 lamps (included), Neutral White 4000K, Electronic Ballast, DALI dimmable, 68W, 4540lm, LOR 92%, Push-in Connector, IP20, IK07, Glow Wire test 960°C, UGR<16, LM65<1000cd/m2.



PRODUCT OVERVIEW

Product name	RANA R 600 Bright Louvre 4x14W DALI MPM 840
Technology	T5
Cap/Base	G5
Housing	Steel
Mount	Ceiling recessed mounting
Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
E-number FI	4289021
E-number Norway	3319754
Warranty	2 years
Fixture luminous flux (lm)	4540
Luminaire efficacy (lm/W)	67
LOR (%)	92
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	85
Glare control	< 16
Light source included	0002761
Total power consumption (W)	68
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	3
Housing colour	White
IP rating	IP20
IK rating	IK07
Product EAN number	5410288497105

RANA T5 600

RANA R 600 Bright Louvre 4x14W DALI MPM 840

0049710

DATA TABLE

General data

Product name	RANA R 600 Bright Louvre 4x14W DALI MPM 840
Technology	T5
Cap/Base	G5
Housing	Steel
Mount	Ceiling recessed mounting
Environment	Interior
General application	Education, Hospitality, Office, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4289021
E-number Norway	3319754
Warranty	2 years

Optical data

Fixture luminous flux (lm)	4540
Luminaire efficacy (lm/W)	67
LOR (%)	92
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	85
Adjustable chromaticity	N
Distribution type	Symmetric
Glare control	< 16

Electrical data

Light source included	0002761
Total power consumption (W)	68
Mains voltage (V)	220-240V
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Transformer required	Yes
Dimmable	Yes
Dimming method	DALI
Minimum dimming level (%)	3
Glow Wire Test (°C)	960
Energy Efficiency Class (A->G) of contained light source	F
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	White
IP rating	IP20
IK rating	IK07
Reflector finish	High-gloss

RANA T5 600



RANA R 600 Bright Louvre 4x14W DALI MPM 840
0049710

Nominal Product Length (mm)	594
Nominal Product Width (mm)	595
Nominal Product Height (mm)	46
Weight (kg)	3.94
Recessed Depth (mm)	120

Packaging

Single packaging type	Carton
Product EAN number	5410288497105
Packaging single length / height (cm)	62.5
Packaging single width (cm)	7.0
Packaging single depth (cm)	61.0
DUN14 (outer)	05410288497105
Units per outer package	1
Packaging outer length / height (cm)	62.5
Packaging outer width (cm)	7.0
Packaging outer depth (cm)	61.0

PHOTOMETRY



TECHNICAL DRAWINGS

