

## Wall-mounted swivelling crane Boy (BW) – with standard chain hoist

With retractable boom



### Application:

The folding boom makes it ideal for loading machines or confined spaces

### Execution:

- Classification in accordance with EN 13001 HC2 S2 HD2 for lightweight industrial applications in production halls
- Round cable power supply in the boom profiles right up to the boom tip
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with bracket suspension – two-stage lifting speed



### Advantage:

- Folding boom
- Fast handling of workpieces
- Swivel resistance is adjusted manually as standard

### Delivery:

Includes detailed documentation, electric chain hoist with bracket suspension

<b>Art. no.</b>	<b>77110 001</b>
<b>Brand</b>	VETTER
<b>Manufacturer Part Number</b>	BW1,25-3,0+SIXX1F
<b>Model</b>	Boy BW
<b>Type</b>	Console assembly A
<b>Load-carrying capacity</b>	125 kg
<b>Overhang</b>	3000 mm
<b>Overhang 1</b>	1600 mm
<b>Overhang 2</b>	1400 mm
<b>Construction height</b>	940 mm
<b>Max. lift height</b>	5 m
<b>Design</b>	With electric chain hoist
<b>Lifting device design</b>	With electric chain hoist SIXX-BL
<b>Swivel range</b>	180 Degree
<b>Colour</b>	Daffodil yellow RAL 1007
<b>Surface</b>	Lacquered
<b>Operating voltage</b>	400 V
<b>Cable length</b>	3.8 m
<b>Weight</b>	151 kg
<b>Max. vertical force</b>	3 kN
<b>Max. horizontal force</b>	10 kN
<b>Gross Weight</b>	173.000 kg
<b>Product Group</b>	7EL