

93520 300 W 82 V

Halogen lamps with reflector MR13



Product datasheet

Technical data


Electrical data

Nominal wattage	300 W
Nominal voltage	82.0 V

Light technical data

Focal length	152.5 mm
--------------	----------

Dimensions & weight



Diameter	42.0 mm
Length	44.5 mm

Lifespan

Lifespan	70 h
----------	------

Additional product data

Base (standard designation)	GX5.3
-----------------------------	-------

Capabilities

Burning position	s90
------------------	-----

Certificates & standards

EEI - Energy Label	E
--------------------	---

Country specific categorizations


ANSI code	FHS
Order reference	93520 300W 82V

Product datasheet

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4050300350196	OSRH93520	-	-	-

Product datasheet



Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300350196	93520 300 W 82 V	Folding carton box 1	58 mm x 47 mm x 48 mm	0.13 dm ³	30.00 g
4050300350202	93520 300 W 82 V	Shipping carton box 24	195 mm x 137 mm x 152 mm	4.06 dm ³	822.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.