


# CLASSICline

Made from high quality tool steel, high gloss mirror polished, box joint, with dissipative ergonomically formed bicoloured hand guard and replaceable double leaf spring.

The pliers of this program have been tested with great results according to DIN EN 61340-5-1, 61340-2-1 as well as 61340-2-3 for work in ESD protected areas.



dissipative, ergonomically formed bicoloured hand guard



3-902-7



3-905-7



3-906-7



3-931-7



3-932-7




3-603-15



3-945-7



3-604-15



3-604-15



## ESD ELECTRONIC PLIERS CLASSICline 2.0

### CUTTING PLIERS

| No. | Length<br>mm | Head width<br>mm | Cutting shape | Cutting capacity |        |      | Wire Ø mm | Weight<br>g |
|-----|--------------|------------------|---------------|------------------|--------|------|-----------|-------------|
|     |              |                  |               | soft             | middle | hard |           |             |

#### Side cutters

with slim, rounded head

|          |     |    |            |     |     |     |    |
|----------|-----|----|------------|-----|-----|-----|----|
| 3-601-15 | 115 | 11 | semi flush | 1.5 | 1.2 | 0.4 | 70 |
| 3-602-15 | 115 | 11 | flush      | 1.5 | 1.2 | -   | 70 |

#### Side cutters

with slim, pointed head and special flat cutting edge

|          |     |    |            |     |     |     |    |
|----------|-----|----|------------|-----|-----|-----|----|
| 3-603-15 | 115 | 11 | semi flush | 1.5 | 1.2 | 0.3 | 65 |
| 3-604-15 | 115 | 11 | flush      | 1.5 | 1.2 | -   | 65 |

#### End cutters

with angled tips 30° and oblique cutting edge

|          |     |      |       |     |     |   |    |
|----------|-----|------|-------|-----|-----|---|----|
| 3-606-15 | 120 | 10.5 | flush | 0.8 | 0.6 | - | 55 |
|----------|-----|------|-------|-----|-----|---|----|

#### Oblique front cutter

Cutting surface angled 15°

|          |     |      |       |     |     |   |    |
|----------|-----|------|-------|-----|-----|---|----|
| 3-625-15 | 120 | 10.5 | flush | 1.5 | 1.2 | - | 90 |
|----------|-----|------|-------|-----|-----|---|----|

#### Top cutters

17 mm wide cutting edge

|          |     |      |       |     |     |   |    |
|----------|-----|------|-------|-----|-----|---|----|
| 3-627-15 | 120 | 10.5 | flush | 1.5 | 1.2 | - | 85 |
|----------|-----|------|-------|-----|-----|---|----|