

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2165711003](#)
Status: **Active**
Overview:
Description: Micro-Fit+ Vertical Header, 3.00mm Pitch, Single Row, 3 Circuits, Matte Tin (Sn) Plating, UL 94V-0, Glow-Wire Capable, Black

General

Product Family	PCB Headers
Series	216571
Application	Power, Wire-to-Board
Overview	microfit_connector
Product Name	Micro-Fit+
UPC	193264921676

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	High Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.499/g
Number of Rows	1
Orientation	Vertical
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	2165710002-PK-000
Product Specification	2064600000-PS-000
Sales Drawing	2165710003-SD-000
Test Summary	2157590005-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[216571](#) Series