



### Main

|                             |   |
|-----------------------------|---|
| Range                       | Clario<br>Acti 9<br>Prodis<br>Librio  |
| Range of product            | Librio<br>ProDis<br>DPN Vigi<br>C120<br>C60<br>DPN<br>ID<br>I-NA<br>Clario  |
| Product or component type   | OC contact  |
| Device short name           | OF  |
| Signal contacts composition | 1 C/O   |
| [In] rated current          | 3 A at 380...415 V AC - 50/60 Hz<br>6 A at 220...240 V AC - 50/60 Hz<br>1 A at 130 V DC<br>1.5 A at 60 V DC<br>2 A at 48 V DC<br>6 A at 24 V DC |
| 9 mm pitches                | 1   |

### Complementary

|                     |   |
|---------------------|---|
| Range compatibility | Acti 9 C120<br>Acti 9 C60H-DC<br>Acti 9 iDPN<br>Acti 9 DPN Vigi<br>Acti 9 RCCB-ID<br>Acti 9 C60PV-DC<br>Acti 9 C40<br>Acti 9 ID C40<br>Acti 9 DT40<br>Acti 9 DT60 |
|---------------------|---|

Acti 9 IDc  
 Acti 9 C120NA-DC  
 Acti 9 ITG40  
 Acti 9 SW60-DC  
 Acti 9 C60NA-DC

|                         |  |
|-------------------------|--|
| Mounting mode           | Fixed  |
| Mounting support        | DIN rail   |
| Height                  | 85.3 mm  |
| Width                   | 9 mm   |
| Depth                   | 78.5 mm  |
| Product weight          | 30 g   |
| Colour                  | White  |
| Connections - terminals | Clamp terminal in bottom 2 cable(s) 1.5 mm <sup>2</sup> flexible<br>Clamp terminal in bottom 1 cable(s) 0.5...2.5 mm <sup>2</sup> rigid<br>Clamp terminal in bottom 2 cable(s) 1.5 mm <sup>2</sup> flexible with ferrule |
| Wire stripping length   | 9 mm   |
| Tightening torque       | 1 N.m  |
| Product compatibility   | C60PV-DC<br>DT40<br>DT60<br>ID C40<br>C40<br>DPN Vigji<br>C120NA-DC<br>C120<br>C60NA-DC<br>ITG40<br>IDc<br>C60<br>SW60-DC<br>IDPN<br>C60H-DC   |
| Market segment          | Residential<br>Small commercial  |

## Environment

|                                       |                                     |
|---------------------------------------|-------------------------------------|
| Standards                             | EN/IEC 60947-5-1                    |
| Product certifications                | KEMA<br>LCIE<br>ASTA<br>ASEFA       |
| IP degree of protection               | IP20 conforming to EN/IEC 60947-5-1 |
| Pollution degree                      | 3 conforming to EN/IEC 60947-5-1    |
| Tropicalisation                       | 2 conforming to EN/IEC 60947-5-1    |
| Relative humidity                     | 95 % at 55 °C                       |
| Ambient air temperature for operation | -25...50 °C                         |
| Ambient air temperature for storage   | -40...85 °C                         |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1001 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available<br><a href="#">Product environmental</a>  |
| Product end of life instructions | Available<br><a href="#">End of life manual</a>   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|