

AC-DC Regulated Switching Power Adapter

7.2 W, Euro plug



FEATURES:

With over voltage, over current and over power protection

L.P.S (Limits for power source)

SPECIFICATION:

Output voltage	12 VDC
Power	7.2 W
Connection, primary side	Euro plug
Connection, secondary side	2.1 x 5.5 x 12 mm Barrel plug
Input voltage	100...240 VAC
MTBF	50 000 Hours min
Output current	0...0.6 A
Noise test bandwidth	20 MHz
Dimensions L x W x H	68.4 x 38.7 x 68.4 mm
Input frequency	50...60 Hz
No load power consumption	< 0.3 W
Line regulation	0.5 %
Operating temperature max.	40 °C
Operating temperature min.	0 °C
Short-circuit-proof	Yes
Weight	95 g
Appliance	Class II
Efficiency	Efficiency level V



Art. Nr.

RND 320-00024

For more information and technical drawings, please contact us at info@distrelec.com.

