

# AC-DC Regulated Switching Power Adapter

## 3.6 W, Euro plug



### FEATURES:

With over voltage, over current and over power protection

L.P.S (Limits for power source)

### SPECIFICATION:

Output voltage	3.0/4.5/5.0/6.0/7.5/9.0/12 VDC
Power	5 W
Connection, primary side	Euro plug
Connection, secondary side	8XC25 + FUSB1
Input voltage	100...240 VAC
MTBF	50 000 Hours min
Output current	600 mA @ 3.0/4.5/5.0 V, 500 mA @ 6.0 V, 480 mA @ 7.5 V, 400 mA @ 9.0 V, 300 mA @ 12 V
Cable length	1.8 m
Dimensions L x W x H	68.4 x 38.7 x 49.4 mm
Input frequency	50...60 Hz
No load power consumption	< 0.3 W
Line regulation	0.5 %
Operating temperature max.	25 °C
Operating temperature min.	0 °C
Short-circuit-proof	Yes
Weight	95 g
Appliance	Class II
Efficiency	Efficiency level V



### Art. Nr.

**RND 320-00044**

For more information and technical drawings, please contact us at [info@distrelec.com](mailto:info@distrelec.com).

