

Accessory

PICO-LPG-780-1064-MEDICAL-BOX
Order Number: 70146721

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-20		40	°C
Storage Temperature	-50		50	°C

Optical Parameters

LB Rating	190-315 D LB8 + IR LB4 315-420 DIR LB5 420-445 DIR LB4 765-1100 DIRM LB5 775-1085 D LB5 + IRM LB6 790-1080 D LB6 + IRM LB7 950-1085 DIRM LB6
Lens Color	Grün

Mechanical Parameters

Material	Plastic
Weight	150 g

(*) Over the complete operating temperature range

Features




- Laser glasses for infrared wavelengths
- Incl. wall holder
- Stickers with mandatory and hazard sign
- Used for medical laser applications

Picture



Safety Label



Valid Revision

| 28-OCT-2020