

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022111041](#)

Status: **Active**

Overview: [Mini-Latch™ Wire-to-Board System](#)

Description: [Mini-Latch™ Wire-to-Board Header, Vertical, with Friction Ramp, 4 Circuits, Gold \(Au\) Plating](#)

Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-5045-003 \(PDF\)](#)

[Product Specification PS-5045-004 \(PDF\)](#)

[Packaging Specification SPK-5045-002-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification


UL E29179

General

Product Family	PCB Headers
Series	5045
Application	Signal, Wire-to-Board
Overview	Mini-Latch™ Wire-to-Board System
Product Name	KK®
UPC	800753733176

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	431.000/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.40mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.356µm
Plating min - Termination	0.356µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[5045 Series](#)

Mates With

KK® 2.50mm Housings [51191](#) , [5051](#)

Electrical

Current - Maximum per Contact 3.0A
Voltage - Maximum 250V

Material Info

Engineering Number 5045-04AG

Reference - Drawing Numbers

Packaging Specification SPK-5045-002-001
Product Specification PS-5045-003, PS-5045-004
Sales Drawing SD-5045-001

This document was generated on 04/20/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION