


FEX FEX 1919 18 G



Sample photo

Order symbol: FEX 1919 18 G
Product nbr: 4130810
Description: Enclosure, PC
Remarks: Ex e II, EN 60079; IK 4J

EAN: 6418074007896
EI. number:
 Finland: 3424640
 Electric No. Denmark: 8212026324
 Electric No. Italy: 7801115
 Electric No. Sweden: 4130810

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	188	188	180	EKJVT	Mounting plate
inch:	7.4	7.4	7.1	EKMVT	Mounting plate
Materials:				EKOVT	Mounting plate
Material:	Polycarbonate			EKPVT	Mounting plate
Base colour:	RAL 7035 -light grey			EKTVT	Mounting plate
Cover screws material:	Polyamide			EKUVT	Mounting plate
Cover colour:	RAL 7035 -light grey			EKV 12	DIN-35 Mounting rail
Cover screws colour:	Grey			EKV 22	DIN-35 Mounting rail
Gasket material:	Silicone			EKV 32	DIN-35 Mounting rail
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP54	
Temperature °C (continuous):	-10 ... 80 °C			Electrical insulation: Totally insulated	
Temperature °F (short term):	-40 ... 250 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (continuous):	14 ... 175 °F			Impact Resistance (EN 50014): 4J	
Accessories:				Certificates:	
EKHVT	Mounting plate			ATEX	
				Attestation of Conformity	

