

## SVJC clamp holder positive, right-hand

For copying, longitudinal and face turning with VC indexable insert

**ATORN**<sup>®</sup>

### Application

For copying, longitudinal and face turning with VC indexable insert 35°

### Version

- Precision-manufactured steel support, burnished, hardened, type V, working angle 93°, tip angle 35°, clearance angle 7°

### Advantage

- Very narrow geometry optimised for contour-turning work
- Positive body geometry ensures low cutting forces
- Very good surfaces, for medium and finishing infeed



<b>Art. no.</b>	<b>17833 042</b>
<b>ISO name</b>	SVJC R/L2525 M11
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Length of head</b>	25.5 mm
<b>Programming size</b>	32 mm
<b>Suitable for indexable inserts</b>	VC.. 1103..
<b>Tool design</b>	Right
<b>DIN</b>	4983

### EAN-Code

4050293346671