

Round nozzle

for stainless steel jointed hose systems

ORION[®]

Application:

For exact and precise cooling.

Execution:

- made from rust-free stainless steel (1.4301)
- suitable up to at least 40 bar operating pressure
- with short combinations, positive operating pressures up to 80 bar are possible
- SW 11 and 16 width across flats on 6-mm system
- Clamping width 14 and 20 across flats on 8.8-mm system

Advantage:

- extremely long service life, resistant to corrosion
- resistant to temperature and chemical substances
- fully rigid and individually adjustable thanks to screw coupling
- will not push away due to pressure, vibration or chips



Art. no.	18300 426
Brand	ORION
Manufacturer Part Number	18300426
Type	Round nozzle, diameter 2 mm
System design	6 mm
Gross Weight	0.013 kg
Product Group	1FH

EAN

4053625199068