

Grinding and control vice OP-S

Actuation via hexagon socket key

ORION[®]

Application:


For horizontal, vertical and lateral grinding, inspection and eroding tasks.

Execution:

- Made of alloyed tool steel.
- Hardened and precision-ground.
- Quick adjustment.
- Horizontally ground vee block.
- Perpendicularity tolerance 0.005 mm/100 mm (base surface to fixed jaw clamping surfaces).
- Parallelism tolerance 0.005 mm/100 mm (base surface to upper guide plate).

Delivery:

1x grinding and control vice OP-S; incl. Hexagon socket wrench



Art. no.	28600 320
Brand	ORION
Manufacturer Part Number	28600320
Prism countersunk horizontally	Yes
Jaws width	50 mm
Jaws height	25 mm
Clamping width	80 mm
Height	53 mm
Base body length	150 mm
Base body width	50 mm
Base body height	28 mm
Gross Weight	1.600 kg
Product Group	282

EAN

4053625621309