

# AL-60P01A

## SPECIFICATIONS:


TYPE	UNIT	AL-60P01A
• Min. Sound Output at 10cm	dB	80
Rated Voltage	V	1.5
Operating Voltage	V	1~2
Resonant Frequency	Hz	2.048
• Max. Current Consumption	mA	15
Coil Resistance	$\Omega$	42 $\pm$ 6
•• Coil Impedance	$\Omega$	120
Operating Temperature	$^{\circ}$ C	-20~+60
Storage Temperature	$^{\circ}$ C	-30~+70
Weight	g	2

• Value applying at (rated voltage, 2.048Hz, 1/2 duty square wave)

•• Value applying at (2.048Hz, sine wave, measuring current 60 $\mu$  A)

## DIMENSIONS :

(Unit: mm)



## Frequency response:

