


# Pluggable Terminal Blocks

## 5 mm Pitch, Reversed



Reversed (Latches are on wire entry side)

Polarised mouldings

Withstand Voltage - AC2000V/1Min

Guided pin alignment

### SPECIFICATION:

Gender of contacts	Female
Rated current to EN	15 A
Pitch	5 mm
Component type	Wire plug straight
Termination type	Screw Connection
Connection direction	vertical
Rated voltage to EN	250 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-33...+120 °C
Cross-section max.	3.3 mm <sup>2</sup>
Cross-section min.	0.2 mm <sup>2</sup>
Connection cross-section	0.2-3.31 mm <sup>2</sup> (24-12AWG)

### PRODUCT RANGE:

Art. Nr.	Poles	A	Length
RND 205-00342	2	10 mm	10 mm
RND 205-00343	3	15 mm	15 mm
RND 205-00344	4	20 mm	20 mm
RND 205-00345	5	25 mm	25 mm
RND 205-00346	6	30 mm	30 mm
RND 205-00348	8	40 mm	40 mm
RND 205-00349	9	45 mm	45 mm