





## Mounting plates

### Order Information

| <br><small>06102501</small>   |                       |                                  | <b>Mounting plate<br/>can be used in combination<br/>with cover plate</b><br><br><small>bza45819</small> | <b>Mounting plate</b>  |                |
|--|-----------------------|----------------------------------|---|--|----------------|
|  |                       |                                  | <b>for use without cover plate</b><br><br><small>06102501</small>                                       | <b>Fixing strip for partial widths</b><br><br><small>06102501</small> |                |
| <b>Width W</b><br><b>HP</b>  | <b>W</b><br><b>mm</b> | <b>Board length</b><br><b>mm</b> | <b>1 piece</b>  | <b>1 piece</b>   | <b>1 piece</b> |
| 28   | 146.88                | 160                              | 34563-001   | 34562-745  | 30840-021      |
| 28   | 146.88                | 220                              | 34563-009   | 34562-749  | 30840-033      |
| 28   | 146.88                | 280                              | —   | 34562-753  | 30840-045      |
| 28   | 146.88                | 340                              | —   | 34562-757  | 30840-057      |
| 42   | 217.99                | 160                              | 34563-002   | 34562-746  | 30840-021      |
| 42   | 217.99                | 220                              | 34563-014   | 34562-750  | 30840-033      |
| 42   | 217.99                | 280                              | —   | 34562-754  | 30840-045      |
| 42   | 217.99                | 340                              | —   | 34562-758  | 30840-057      |
| 63   | 324.67                | 160                              | 34563-003   | 34562-747  | 30840-021      |
| 63   | 324.67                | 220                              | 34563-019   | 34562-751  | 30840-033      |
| 63   | 324.67                | 280                              | —   | 34562-755  | 30840-045      |
| 63   | 324.67                | 340                              | —   | 34562-759  | 30840-057      |
| 84   | 431.35                | 160                              | 34563-004   | 34562-748  | 30840-021      |
| 84   | 431.35                | 220                              | 34563-024   | 34562-752  | 30840-033      |
| 84   | 431.35                | 280                              | —   | 34562-756  | 30840-045      |
| 84   | 431.35                | 340                              | —   | 34562-760  | 30840-057      |
| Assembly kit for mounting plate, PU 1 kit<br>(Torx countersunk screw M4 x 5, St,<br>zinc-plated, 12 pieces;<br>screw M4 x 6, St, zinc-plated, 10 pieces;<br>square nut M4, St, zinc-plated, 10 pieces) |                       |                                  | 24560-184   | 24560-184  | —              |
| Assembly kit for fixing strips for partial width<br>mounting plates<br>Torx screw M2.5 x 5, St, zinc-plated,<br>PU 100 pieces  |                       |                                  | —   | —  | 24560-146      |

### Note

- For installation and fixing of heavy components
- In addition to the mounting plate, (EMC) cover plates can also be fitted to the subrack
- The mounting plate is as wide as the subrack or system case and is fixed to the side panels
- A guide rail can be fitted on the first and last slot
- Guide rails type "4.4" and type "strengthened" cannot be used