

Coaxial Cable Connector 11_SMA-50-3-5/111_N

Description

Straight cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 18 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Outer contact 0.0045 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Bronze	
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	

Related Documents

Outline drawing DOU-00006091
Catalogue drawing DOU-00006088
Assembly instruction DOC-0000179078

Ordering Information

Bulk 100 pcs package 11_SMA-50-3-5/111_NH
Single package 11_SMA-50-3-5/111_NE

Additional Information

Suitable cables RG_58_C/U, G_03232