



Dead Blow & Sledge Hammers



802 Dead Blow, Medium Hard Face Hammer, Recoilless, Polyurethane, Steel Tube Shaft. "GS" Sign, Cushion Grip.
 Preserves sensitive surfaces & edges, increases striking power & avoid hand fatigue.
Application: Machine tools & gear box construction, sheet metal & repair shops.
 Faces polyurethane, shatterproof, wear resistant, extremely durable
 Faces replaceable. Tubular handle, lacquered in blue, cushion grip.

Item No.	mm	Inch	mm	Inch	mm	Inch	oz.	pkg.
80225	25	1.0	106	4.2	288	11.3	18	1
80230	30	1.2	115	4.5	290	11.4	21	1
80235	35	1.4	118	4.6	300	11.8	24	1
80240	40	1.6	125	4.9	305	12.0	30	1
80245	45	1.8	130	5.1	310	12.2	37	1
80250	50	2.0	130	5.1	365	14.4	49	1
80260	60	2.3	156	6.1	375	14.7	72	1
80270	70	2.8	161	6.3	385	15.1	97	1




Medium Hard Faces



800 Dead Blow, Recoilless, Polyurethane Face, Hickory Handle
Application: Tools, engineering gear box construction, Sheet metal & repair shops, heavy industry. Steel head for incredible strength. Faces polyurethane, shatterproof, wear resistant, extremely durable. Faces replaceable. Hickory handle.

Item No.	mm	Inch	mm	Inch	mm	Inch	oz.	pkg.
80025	25	1.0	106	4.2	320	12.5	11	1
80030	30	1.2	113	4.4	350	13.7	16	1
80035	35	1.4	115	4.5	355	13.9	20	1
80040	40	1.6	123	4.8	375	14.7	26	1
80045	45	1.8	130	5.1	380	14.9	35	1
80050	50	2.0	134	5.3	385	15.1	44	1
80060	60	2.3	158	6.2	420	16.5	70	1
80070	70	2.8	158	6.2	430	16.9	91	1



Medium Hard Faces

802 Dead Blow Sledge, Recoilless, Polyurethane Face, Hickory Handle
Application: Tools, engineering gear box construction, Sheet metal & repair shops, heavy industry. Polyurethane, shatterproof faces replaceable. Hickory handle.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
80280	80	3.1	205	8.0	882	34.6	10.0	1
80299	100	3.9	210	8.2	1002	39.3	15.1	1



802 Replacement Hammer Faces - Medium

Item No.	mm	Inch	lbs.	pkg.
80219	80	3.1	.06	1
80222	100	3.9	.10	1




For 800 & 802 Hammers

Medium Hard Faces

802 Replacement Hammer Faces

Item No.	mm	Inch	lbs.	pkg.
80200	25	1.0	.04	1
80202	30	1.2	.04	1
80204	35	1.4	.05	1
80206	40	1.6	.08	1
80208	45	1.8	.12	1
80210	50	2.0	.16	1
80213	60	2.3	.29	1
80216	70	2.8	.39	1



Medium Hard Faces

80290 3 Pc. Dead Blow Hammer Set


Item No.	mm	Inch	lbs.
80290	80230	30	6.35
	80240	40	
	80250	50	



Extra Hard Nylon

802 Replacement Hammer Faces

Item No.	mm	Inch	lbs.	pkg.
80203	30	1.2	.04	1
80207	40	1.6	.04	1
80211	50	2.0	.05	1
80214	60	2.3	.07	1



For Dead Blow Hammers

800 Hickory Replacement Handles

Item No.	Fits Hammer	lbs.	pkg.
80071	80025	25mm	.11 1
80072	80030 & 80035	30/35mm	.19 1
80074	80040 & 80045	40/45mm	.29 1
80076	80050	50mm	.38 1
80078	80060 & 80070	60/70mm	.44 1
80079	80280	80mm	1.76 1
80081	80299	100mm	2.31 1