Fuseholders 6 x 30 mm (1¼"x¼")



🕸 S 🖲 🔁 🚳

16A 250Vac (max fuse rating*) T-55 to T+70 (ambient) Maximum dissipation wattage: 2.5W UL 94V2 UL file E92075 CSA file LR44770

These products comply with safety category PC2 *Users should be aware of the de-rating factors published by specialist manufacturers of fuses

Fuseholders with in-line termination have combination (4.8 / 6.3) terminals. It has not been possible to show both views here. Units with right angle terminals have user specified end terminals and combination mid-body terminals





A0035 00 In-line 6 x 30 1¼ x ¼ fuseholder

Call factory for rating details

TERMINAL BODY & CAP PANEL HOLE OPTIONS

