
## pressure and vacuum switches





## DIAPHRAGM PRESSURE SWITCH WITH 4A RATED CHANGEOVER CONTACTS AND BUILT IN CONNECTOR

- Range from 0.3 1.5 Bar to 10 100 Bar
- Up to 300 Bar overpressure
- SPDT changeover contact
- · Zinc plated steel body
- Nitrile, EPDM, Viton diaphragm seals

Туре 0184


## CHANGEOVER CONTACT DETAILS



TECHNICAL SPECIFICATION					
Contact rating	4A				
Maximum operation	200/min				
Temperature range	NBR -30 to +100°C EPDM -30 to +100°C FKM -5 to +120°C				
Maximum voltage	250VAC				
Hysteresis adj.	10 to 30% (adjusted at factory)				
Mechanical life	10 <sup>6</sup> operations at 50 Bar pressure				
Body material	Zinc plated steel (Fe/Zn 12cC)				
Protection	IP65				

ORDERING INFORMATION   Thread Adjustment range (Bar)   Tolerance at room temp  Static							
Тур	pe 0184	Thread type	Adjustment range (Bar)	(Bar)	Static Overpressure (Bar)		
45702	002	M12 x 1.5	0.3 - 1.5	±0.2	100		
45703	003	1/4" BSP					
45802	041	M12 x 1.5	- 1 - 10	±0.5 - 1.0			
45803	042	1/4" BSP					
45902	008	M12 x 1.5	- 10 - 50	±3.0	300		
45903	009	1/4" BSP		±3.0	300		
46102	011	M12 x 1.5	- 10 - 100	±3.0 - 5.0			
46103	012	1/4" BSP					

SUCO diaphragm type	Material	Suitable for
1	Nitrile (NBR)	Hydraulic oil, engine oil, heating oil, turpentine, air
2	EPDM	Water, Hydrogen, Seawater, Acetylene, Ozone, Oxygen, Brake Fluid
3	Viton (FKM)	Hydraulic fluid (i.e. HFA, HFB, HFC, HFD), Gasoline



## 0800 731 3187 www.oem.co.uk