


BU-4150028-@

(Cable Assembly Coaxial BNC to SMA Male to Male RG-316)





Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector Impedance	Frequency (GHz)	VSWR	Working Voltage	
		(Ohms)			(At Sea	
					Level)	
BNC/SMA	RG-316	50	0-3	1.4 MAX	335V	

Product Attributes

Gender	Male to Male			
Style	BNC to SMA			
1st Connector	BNC Male Plug			
2nd Connector	Gold Plated SMA Male Plug			
Features	Shielded			
Operating Temperature	-65°C (-85°F) to 150°C (302°F)			
BU-4150028006	6" (152.40 mm)			
BU-4150028012	12" (304.8 mm)			
BU-4150028024	24" (609.6 mm)			
BU-4150028036	36" (914.4 mm)			
BU-4150028048	48" (1219.2 mm)			
RoHS 3 Compliant				

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524