


30° Sloped Instrument Console (1456)




KEY FEATURES

Aluminum Top and Case
Same as 10° series (see page 59)

KEY FEATURES

Aluminum Top and Walnut Case
Same as 10° series (see page 59)

Off White Top and Blue Case	Part Number	Black Top and Blue Case	Off White Top and Walnut Case	Units	Dimensions					
					A	B	C	D	E	F
1456CE3WHBU	1456CE3BKBU	1456CE3WHCWW		inch mm	4 102	5.5 140	3 76	1.1 28	3.7 94	2.2 56
1456FE3WHBU	1456FE3BKBU			inch mm	6.5 165	5.5 140	3 76	1.1 28	3.7 94	2.2 56
1456FG4WHBU	1456FG4BKBU			inch mm	6.5 165	7.2 183	4 102	1.1 28	5.7 145	2.2 56
1456KE3WHBU	1456KE3BKBU			inch mm	10 254	5.5 140	3 76	1.1 28	3.7 94	2.2 56
1456KG4WHBU	1456KG4BKBU			inch mm	10 254	7.2 183	4 102	1.1 28	5.7 145	2.2 56
1456KK4WHBU	1456KK4BKBU	1456KK4WHCWW		inch mm	10 254	10.2 259	4 102	1.1 28	5.7 145	5.2 132
1456PG4WHBU	1456PG4BKBU			inch mm	14 356	7.2 183	4 102	1.1 28	5.7 145	2.2 56
1456PK4WHBU	1456PK4BKBU	1456PK4WHCWW		inch mm	14 356	10.2 259	4 102	1.1 28	5.7 145	5.2 132
1456RK4WHBU	1456RK4BKBU			inch mm	17 432	10.2 259	4 102	1.1 28	5.7 145	5.2 132
1456WK4WHBU	1456WK4BKBU			inch mm	20 508	10.2 259	4 102	1.1 28	5.7 145	5.2 132



Metal