

## ToLEDo Retro GLS Dimmable

ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL

0029319



### Product features

- Perfect for decorative and general lighting applications and creates a warm ambiance similar to traditional lamps
- Same look, size and functionality as incandescent lamps
- Omni-directional light distribution
- Suitable replacement for incandescent and halogen lamps
- Gives same sparkling light effect as incandescent lamp
- Dimensionally identical to incandescent lamps - fits all fixtures
- Environment friendly - no mercury and lower CO2 emissions
- Dimmable with approved dimmers



### PRODUCT OVERVIEW

Product name	ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL
Technology	LED
Watt (Rated) (W)	9
Type	LED exchangeable
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740904
Warranty	3 years
Luminous flux (lm)	1055
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG1
Wattage (W)	9
Product Voltage (V)	230
Dimmable	Yes
Average life (Nominal) (h)	15000
Product EAN number	5410288293196

### DATA TABLE

#### General data

Product name	ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL
Technology	LED

## ToLEDo Retro GLS Dimmable

ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL

0029319

Watt (Rated) (W)	9
Type	LED exchangeable
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Operating temperature range (°C)	-10°C...+45°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740904
Warranty	3 years

### Optical data

Luminous flux (lm)	1055
Luminous flux (Rated) (lm)	1055
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Photobiological Risk Group	RG1
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	9
Equivalent watt (W)	75
Product Voltage (V)	230
Control gear required	No
No. Of switching cycles before premature failures	>50000
Transformer required	No
Dimmable	Yes
Inrush Current (A)	1.5
Inrush Duration (µs)	520
Lamp Energy Label (class)	E
Max. Luminaires per 16A C Breaker	106
Max. Luminaires per 16A B Breaker	54

### Lifetime data

Lifespan L70 B50	15000
Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

### Physical data

Nominal Product Length (mm)	108
Nominal Product Diameter (mm)	60
Weight (kg)	0.064

### Packaging

Single packaging type	Carton
Product EAN number	5410288293196

## ToLEDo Retro GLS Dimmable

ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL


0029319

Packaging single length / height (cm)	12.0
Packaging single width (cm)	6.6
Packaging single depth (cm)	6.6
DUN14 (outer)	15410288293193
Units per outer package	6
Packaging outer length / height (cm)	20.6
Packaging outer width (cm)	13.9
Packaging outer depth (cm)	13.0


### Safety data

Optimal operating condition (°C)	-10-45
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures

## PHOTOMETRY



## TECHNICAL DRAWINGS



# SYLVANIA

## ToLEDo Retro GLS Dimmable


ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL

0029319



### SYLVANIA

0029319



**9**  
kWh/1000h



2019/2015


## ToLEDo Retro GLS Dimmable

ToLEDo RT GLS V5 ST DIM 1055LM 865 E27 SL

0029319



0029319



**9**  
kWh/1000h



2019/2015