

Short-length chucks

ERICKSON system with straight shank

ORION[®]

Application:

For use on NC and CNC machining equipment.

Execution:

- Min. tensile strength at core 800 N/mm.
- Hardened.
- Clamping of drill bits on drill heel possible.
- With adjustable longitudinal stop.
- Collets no. 23326.

Advantage:

- With straight shank - extremely slim version.
- Very good accessibility in confined spaces.

Delivery:

1x ERICKSON short chuck system with cylindrical shank.



Art. no.	23325 315
Brand	ORION
Manufacturer Part Number	23325315
Collet type	DK 20
Shank diameter	20 mm
Min./max. clamping width	1-10 mm
Width across flats	19 mm
Outer diameter	21 mm
Shaft length	140 mm
Length of head	44 mm
Min. clamp in depth	41 mm
Max. clamp in depth	178 mm
Gross Weight	0.309 kg
Product Group	218

EAN

4039247 157006