

Studs



Version:

- Tempered
- Rolled thread
- M 6 to M12 tempered to strength class 10.9
- M14 to M42 tempered to strength class 8.8.



Art. no.	26197 122
Thread dimension	M12
Thread length	15 mm
Thread length 2 (metric thread)	63 mm
Length	100 mm
DIN	6379

EAN-Code

4020772081348